



SHP-30K-HV Series

30kW Industrial Standard Three-Phase HVDC Power System

- 3 ψ 3-wire / Δ or Y 340~530VAC or 3 ψ 4-wire / Y 340~530VAC
- High efficiency up to 97%
- Up to 120% peak power capability
- 2U high 19"-inch rack with forced air cooling
- Built-in CANBus/Optional PMBus/MODBus-RTU/RS-485 protocol
- Output voltage and constant current level programmable
- Active current sharing up to 12 units(285KW) and more
- Built-in remote ON-OFF control / Auxiliary power / Alarm signal / Fan fail
- Protections: Short circuit / Overload / Over voltage / Over temperature
- Double insulation for 55V model
- 5 years warranty

Agriculture Machinery Charging Solution



HEADQUARTERS (Taiwan)

- www.meanwell.com
- +886-2-2299-6100
- info@meanwell.com

MEAN WELL USA

- www.meanwellusa.com
- +1-833-635-7201
- info@meanwellusa.com

MEAN WELL EUROPE

- www.meanwell.eu
- +31-20-758-6000
- info@meanwell.eu



SPEC.