



工业用



资通讯



医疗用



居家用

LOP 系列

超薄基板型电源供应器

- 明纬专利号 ZL 202223277512.1
- 4"x2" 和 5"x3" 低高度小巧外型 (25.4mm~33.5mm)
- 全球安规多领域认证 (资通讯62368-1、医疗60601-1、家用60335-1、工业用61558-1/-2-16)
- 设计符合2xMOPP, 适用于BF类医疗应用
- 可提供150% 峰值功率达3秒
- 适用于Class I 或 Class II 系统
- 工作温度 -40~+80°C
- 保护功能: 短路、过载、过压、过温保护
- 极低漏电流 (对地<500μA、接触<70μA)
- 可操作于5,000米高海拔
- 过电压级别OVCI
- 3年保固

规格介绍



UL62368-1
ANSI/AAMI ES60601-1

BS EN/EN62368-1
BS EN/EN60335-1
BS EN/EN61558-1/-2-16
BS EN/EN60601-1

IEC62368-1
IEC60335-1
IEC61558-1/-2-16
IEC60601-1

AS/NZS 61558-1/-2-16 GB4943.1 TPTC004

	4"x 2"		5"x 3"		
系列	LOP-200	LOP-300	LOP-400	LOP-500	LOP-600
机型	12V/ 15V/ 18V/ 24V/ 27V/ 30V/ 36V/ 48V/ 54V		12V/ 15V/ 18V/ 24V/ 27V/ 36V/ 48V/ 54V		
尺寸 (长x宽x高)	101.6x 50.8x 25.4mm		127x 76.2x 27.5mm	127x 76.2x 30.5mm	127x 76.2x 33.5mm
自冷瓦数	140W	180W	250W	320W	400W
外加风扇瓦数	200W	300W	400W	500W	600W
峰值功率 (3秒)	300W	450W	600W	750W	900W
工作温度	-40 ~ +80°C				
过电压级别	OVCIII				
耐压 (I/P-O/P)	4KVAC				
绝缘保护	2 x MOPP				
安规认证	CB / TUV / UL / RCM / CCC / EAC / CE / UKCA (Class I 和 Class II 皆有证书)				
	62368-1 + 60601-1 + 61558-1/-2-16 + 60335-1				

订购资讯

LOP-400-12

输出电压 (12V/ 15V/ 18V/ 24V/ 27V/ 30V/ 36V/ 48V/ 54V)

额定功率 (200W, 300W, 400W, 500W, 600W)

系列名称



明纬(广州)电子有限公司

www.meanwell.com.cn

info@meanwell.com.cn

400-800-3608(业务专线)

020-3773-7100

苏州明纬科技有限公司

www.meanwell.cc

info@meanwell.cc

0512-6508-8600



明纬公众号

有关产品资讯、报价及
技术支持请洽：