



工業用



資通訊



醫療用



居家用

LOP 系列

超薄基板型電源供應器

- 明緯專利號 ZL 202223277512.1
- 4"x2" 和 5"x3" 低高度小巧外型 (25.4mm~33.5mm)
- 全球安規多領域認證 (資通訊62368-1, 醫療60601-1, 家用60335-1, 工業用61558-1/-2-16)
- 設計符合2xMOPP, 適用於BF類醫療應用
- 可提供 150% 峰值功率達3秒
- 適用於Class I 或 Class II 系統
- 工作溫度 -40~+80°C
- 保護功能: 短路、過載、過壓、過溫保護
- 極低漏電流 (對地<500μA、接觸<70μA)
- 可操作於5,000米高海拔
- 過電壓級別OVC III
- 3年保固

規格介紹



UL62368-1
ANSI/AAMI ES60601-1



BS EN/EN62368-1
BS EN/EN60335-1
BS EN/EN61558-1/-2-16
BS EN/EN60601-1



IEC62368-1
IEC60335-1
IEC61558-1/-2-16
IEC60601-1



AS/NZS 61558-1/-2-16



GB4943.1



TPTC004



	4"x 2"		5"x 3"		
系列	LOP-200	LOP-300	LOP-400	LOP-500	LOP-600
機型	12V/ 15V/ 18V/ 24V/ 27V/ 30V/ 36V/ 48V/ 54V		12V/ 15V/ 18V/ 24V/ 27V/ 36V/ 48V/ 54V		
尺寸 (長x寬x高)	101.6x 50.8x 25.4mm		127x 76.2x 27.5mm	127x 76.2x 30.5mm	127x 76.2x 33.5mm
自冷瓦數	140W	180W	250W	320W	400W
外加風扇瓦數	200W	300W	400W	500W	600W
峰值功率 (3秒)	300W	450W	600W	750W	900W
工作溫度	-40 ~ +80°C				
過電壓級別	OVCIII				
耐壓 (I/P-O/P)	4KVAC				
絕緣保護	2 x MOPP				
安規認證	CB / TUV / UL / RCM / CCC / EAC / CE / UKCA (Class I 和 Class II 皆有證書)				
	62368-1 + 60601-1 + 61558-1/-2-16 + 60335-1				

訂購資訊

LOP-400-12

輸出電壓 (12V/ 15V/ 18V/ 24V/ 27V/ 30V/ 36V/ 48V/ 54V)

額定功率 (200W, 300W, 400W, 500W, 600W)

系列名稱



有關產品資訊、報價及技術支援請洽：
明緯企業股份有限公司 業務部



www.meanwell.com.tw



(02)2299-6100



info@meanwell.com



基板型電源館