

LCM-40/60ZB
LED Driver with ZigBee Solution



- ZigBee wireless control technology
- Support ZigBee controller or Gateway control
- Mesh network nodes support



Driver Selection MEAN WELL ELG / LCM / NPF / PWM ZB series

WPD-06
Multi-channel LED Dimmer with EnOcean Solution



- EnOcean wireless control technology
- Easy installation and configuration
- 6 protected and independent dimming output channels
- Up to 128 wireless batteryless switches
- Suitable for constant voltage lighting application
- Up to 30 meter wireless distances



Driver Selection MEAN WELL LED drivers with C.V. mode

iTouch
Wireless Smart Home Controller



- RF/WiFi/IR Remote control
- Free iOS /Android APP download and big data accessibility
- Smart scenes for Home Automation and Lighting Control Systems
- Easy installation and configuration
- Energy saving and monitoring



Driver Selection MEAN WELL LED Driver with 3-in-1 dimming function

LCM-25/40/60DA with DAP-04
LED Driver with DALI Solution



- DALI interface
- Easy lighting group setting and operation
- Easy installation and configuration



Driver Selection ELG / LCM / NPF / PWM with DA series

ELG-150-C1400PLC
LED Driver with PLC Solution

- Power line carrier technology
- Dimming control via power line communication
- Easy installation and configuration



Driver Selection MEAN WELL ELG with PLC series

HLG/ELG LED Power Supply LED Driver

- Constant current & constant voltage output
- Suitable for outdoor LED lighting



Driver Selection HLG 40~600H series
ELG 75~240 series

PIR-045
PIR (Passive Infrared) Dimming Sensor

- Built-in Passive Infrared sensor module
- MCU controller, no relay contact
- Adjustable off-time delay / dimming level / sensitivity



Driver Selection MEAN WELL LED Driver with 3-in-1 dimming or 12Vdc auxiliary

**RFP-M1M3-3A
RFP-M2M3-3A
RFP-M5M3-3A
RFP-M8M4-5A**
Multi-functional LED Dimmer & LED Controller

- RF wireless remote control
- Adjustable brightness / color temperature / RGBW
- Suitable for LED strips application



Driver Selection MEAN WELL LED drivers with C.V. mode

POB-30 Series
AC plug-in LED Module


- AC mains direct driving
- Systematic efficacy >100 lm/w @3000K
- CRI>80 ; PF> 0.95
- T.H.D. <20%
- Easy installation and configuration




Driver Selection Other MEAN WELL LED drivers available

**NCL-CL1-01
IRL-CL2-01
IRL-RGB-01
IRL-RGBW-01**
LED Strips

- 12V LED Strips
- Uniform brightness, high stability
- Tailored length per application demand



Driver Selection MEAN WELL switching power supply with 12Vdc





Your Reliable Power Partner

Taiwan (Headquarters)
MEAN WELL ENTERPRISES CO., LTD.
No. 28, Wuquan 3rd Road, Wugu District,
New Taipei City, Taiwan, 24891
Tel +886-2-2299-6100(rep.)
Fax +886-2-2299-6200(rep.)
+886-2-2298-0818(sales)
e-mail info@meanwell.com
Web www.meanwell.com



info@meanwell.com
www.meanwell.com



Driving Your  Life Intelligently

China
MEAN WELL (GUANGZHOU) ELECTRONICS CO., LTD.
2F, A Building, Yuan Industry Park, Huangcun,
Dongpu Town, Tianhe District, Guangzhou, China
Tel +86-20-2887-1200 +86-755-2359-1630 (Shenzhen Office)
Fax +86-20-8201-0507 +86-20-8201-0507 (Shenzhen Office)
e-mail info@meanwell.com.cn **Web** www.meanwell.com.cn

SUZHOU MEAN WELL TECHNOLOGY CO., LTD.
No.77, Jian-Ming Rd. Dong-Qiao, Pan-Yang Ind. Park, Huang-Dai Town,
Xiang-Cheng District, Suzhou, Jiang-Su, China
Tel +86-512-6508-8600 **Fax** +86-512-6508-8700
e-mail info@meanwell.cc **Web** www.meanwell.cc

U.S.A.
MEAN WELL USA, INC.
44030 Fremont Blvd., Fremont, CA 94538, U.S.A.
Tel +1-510-683-8886 **Fax** +1-510-683-8899
e-mail info@meanwellusa.com **Web** www.meanwellusa.com

Europe
MEAN WELL EUROPE B.V.
Langs de Werf 8, 1185XT Amstelveen, the Netherlands
Tel +31-20-758-6000 **Fax** +31-20-758-6001
e-mail info@meanwell.eu **Web** www.meanwell.eu



December 2015