








HRP(G)-N3
350%
Peak Power

350% High Peak Power Reliable And Durable Industrial Power Supply



Are you still struggling with electro-mechanical equipment, motors or capacitive loads failing to start smoothly? MEAN WELL has launched a new highly reliable high-peak load power supply — HRP(G)-N3 series, which has the following five advantages suitable for all types of industrial automation, logistics and warehousing equipment, household appliances, financial and commercial equipment, and many other applications.



Please contact us for product information, quotations and technical support

HEADQUARTERS (Taiwan)

- www.meanwell.com.tw
- +886-2-2299-6100
- info@meanwell.com

MEAN WELL USA

- www.meanwellusa.com
- +1-510-683-8886
- info@meanwellusa.com

MEAN WELL EUROPE

- www.meanwell.eu
- +31-20-758-6000
- info@meanwell.eu

**Instantaneous peak load up to 350%,
motors or capacitive loads start without difficulty**

The instantaneous peak power required for a motor or capacitive load start-up is many times higher than the nominal power. If your equipment cannot start smoothly and instantly, MEAN WELL's HRP(G)-N3 series will be your best choice!



**-40 to 70°C ultra-wide temperature range,
less environmental limitation**

Global climate change causes extremely cold or high temperatures. If your equipment installation environment is subject to temperature extremes, or if your equipment is installed in a narrow space with poor ventilation, MEAN WELL's HRP(G)-N3 series is your best solution!



**±15% adjustable output voltage range and
high power density design can save costs,
space and increase application flexibility**

If your equipment has limited internal space, and sub-system require different operating voltage, as well as budget considerations, all of which cannot accommodate installing a high wattage large-sized power supply, choose MEAN WELL's HRP(G)-N3 series with 30% of adjustable output voltage and high power density would be your best choice.



**Vibration-resistance up to 5Gs
ensures long-term operation of the equipment**

Since machinery usually produces high vibrations at start-up or during operation, the HRP(G)-N3 series is a one-step design with 5G high-vibration resistance to ensure that the equipment is continuously up and running.



Choose the HRP(G)-N3 series that is right for you

HRP(G)-N3
350%
Peak Power



HRP(G)-N3 Series

- 85 to 264Vac full range input
- Withstand 300Vac surge input for up to 5 seconds
- Up to 350% peak power capability (Max.)
- 1U low profile (150W/300W only)
- Complete safeties and protections
- 5-year warranty
- Suitable for industrial automation, logistics storage equipment, financial commercial, household equipment and other applications

HRP-150N3
Specification Download



HRP-300N3
Specification Download



HRP-600N3
Specification Download



HRP-1000N3
Specification Download



**Share and
Subscribe**

